



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65656 40W 3/4/5K CCT Selectable Small Wall Pack

Satco

Catalog Number	65656
Manufacturer	Satco
Description	40 Watt Small Led Wall Pack With Integrated Bypassable Photocell - CCT Selectable - 120-277 Volts - Dusk to Dawn Security Lighting - IP65 - Bronze Finish
Weight per unit	5.4 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED
Material	ADC12 and PC
Number of Lamps	1
surge protection	Built-in surge protection - 2.5KV
Warranty	5 Year Limited - Fixtures

Material, Color, and Finish

fixture material	Aluminum ADC12 and PC
------------------	-----------------------

Descriptions

Description	40W 3/4/5K CCT SELECTABLE SMALL WALL PACK
extra long description	SATCO 65/656 40W LED SMALL WALL PAC
Long Description	40 Watt Small LED Wall Pack with Integrated Bypassable Photocell - CCT Selectable - 120-277 Volts - Dusk to Dawn Security Lighting - IP65 - Bronze Finish
Product Type	40W Led Small Wall Pack
Special Features	Lawful for sale in California ; Warranty: 5 Year Limited - Fixtures ; Watts: 40 ; Voltage range: 120V-277V ; Lumen range: 4200L-5000L ; CCT: 3000K/4000K/5000K ; CRI: 70 ; Dimmable: Non-Dimmable ; Dimming type: N/A ; Hours Rated: 50000 ; DLC approved: Yes ; Notes: IK10 Lens ; Beam spread: 80 ; Flicker free ; HID equivalent: 150W ; Incandescent equivalent: 300W ; IP65 rated ; Operating temperature: -40C (-40F) to a maximum of +45C (+113F) ; Photocell: Yes - Bypassable

Manufacturer Information

Brand	Nuvo
GTIN	00045923651762
Manufacturers Part Number	65/656
UPC	045923651762



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Wall Pack

Packaging

Carton	1
Weight	5.08
Weight Per each	5.35

Uses, Certifications, and Standards

Application	Security Lighting
environmental conditions	Wet location
Operating Temperature	-40C (-40F) to a maximum of +50C (+122F)
standard	cULus