



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 660RTQ 1/2" Emt Push-In Raintight Coupling

*Crouse-Hinds*

Catalog Number	660RTQ
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Push-In Raintight Coupling, Emt, Zinc Die Cast, Raintight, No Disassembly, 1/2"
Weight per unit	0.1400 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Push In
dimensions	1.3500 IN X 1.2600 IN X 1.3500 IN
Insulation Class	NON INSULATED
Material	Zinc Die Cast

### Material, Color, and Finish

Color	Gray
Finish	Zinc

### Dimensions and Weight

Size	1/2 in
------	--------

### Descriptions

Description	1/2" EMT PUSH-IN RAIN TIGHT COUPLING
extra long description	CRS-H 660RTQ 1/2 EMT PUSH IN CPL RA
Features	Fast installation with no disassembly required! Crouse-Hind series push-in raintight EMT connectors and couplings simply push onto the EMT conduit without the use of any tools or additional labor. Used in raintight environments to join EMT conduit to a box or enclosure, or to couple two ends of EMT conduit. The design prevents water seepage into the conduit, box or enclosure.
Long Description	Eaton Crouse-Hinds series push-in raintight coupling, EMT, Zinc die cast, Raintight, no disassembly, 1/2"
Product Type	1/2 Emt Push In CPL Raintight
Special Features	PUSH IN EMT RAIN TIGHT COUPLING

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662276526075
Manufacturers Part Number	660RTQ
UPC	662276526075



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	Push-in raintight coupling

## Packaging

Carton	1
Weight Per each	0.14

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting standard	Push In cULus