
TRADEMASTER GROUNDING TOGGLE SWITCH, WHITE

660WG | [Pass & Seymour](#)



FEATURES & BENEFITS

Smooth, quiet toggle action single pole switch with high-impact resistant construction and grounded terminals. It is a thermoplastic toggle and frame. It has easy-access green hex head ground screw. 15 amps, 120 volts, White.

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White
Product Series: TradeMaster
Type: Toggle
Number Of Poles: 1
Special Features: Self-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111
CSA Standard: Yes
cULus: Yes
cUL Standard: Yes
UL Listing No: UL20
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.090"
Height (US): 3.281"
Width (US): 1.25"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120VAC

Volts (AC): 120

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: Trade Agreement Act Compliant

TRADEMASTER GROUNDING TOGGLE SWITCH, WHITE

660WG | [Pass & Seymour](#)



FEATURES & BENEFITS

Smooth, quiet toggle action single pole switch with high-impact resistant construction and grounded terminals. It is a thermoplastic toggle and frame. It has easy-access green hex head ground screw. 15 amps, 120 volts, White.

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White

Product Series: TradeMaster

Type: Toggle

Number Of Poles: 1

Special Features: Self-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111

CSA Standard: Yes

cULus: Yes

cUL Standard: Yes

UL Listing No: UL20

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.090"

Height (US): 3.281"

Width (US): 1.25"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120VAC

Volts (AC): 120

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: Trade Agreement Act Compliant