



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



6636G 6X6X36 SC Wireway

Unity MFG

| | |
|------------------|---|
| Catalog Number | 6636G |
| Manufacturer | Unity MFG |
| Description | Unity 6636G Lay-In Wireway, Removable Hinged Cover Type, Length: 36 In, Width: 6 In, 6 In Height, Nema 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 16 Ga Low Carbon Steel, Gunsmoke Gray Powder Coated, Yes Knockouts, C/Us UI 50 and UI 870 - Type 1: Intended For Indoor Use Primarily to Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, Csa C22.2 No. 26 Certified, Type 1, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and Termination, Ho |
| Weight per unit | 15.0 (lbs/each) |
| Product Category | Nema Type 1 Wireway & Fittings |

Features

| | |
|------------|------------------|
| Cover Type | Removable Hinged |
| Knockouts | Yes |
| Material | Low-Carbon Steel |

Material, Color, and Finish

| | |
|--------|-------------|
| Finish | Powder Coat |
|--------|-------------|

Dimensions and Weight

| | |
|--------|----|
| Height | 6 |
| Length | 36 |
| Width | 6 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Construction | Formed From Code Gauge, Low Carbon Steel |
| Description | 6X6X36 SC WIREWAY |
| extra long description | UNT 6636G N1 HINGED COVER WIREWAY W |
| Long Description | Unity 6636G Lay-In Wireway, Removable Hinged Cover Type, Length: 36 IN, Width: 6 IN, 6 IN Height, NEMA 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 16 GA Low Carbon Steel, Gunsmoke Gray Powder Coated, Yes Knockouts, C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And Termination, Ho |
| Product Type | N1 Hinged Cover Wireway With K.O. Powder Coated |
| Special Features | For protecting electrical wiring where dust, dirt, oil and water are not serious problems; All sections and fittings are fully open on one side so wires and cables can be laid in along an entire run; No pulling-through of wires or cables is required; Wireway body has mounting holes on the back; Cover is secured to the body with plated screws; Keyhole slots are furnished on the wireway cover which allow easy access to the inside without removing the screws; 1/2 IN, 3/4 IN, 1 IN, 1-1/4 IN Concentric Knockout |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Unity |
| GTIN | 00761515102701 |
| Manufacturers Part Number | 6636G |
| UPC | 761515102701 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | Lay-In Wireway |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Package | 2 |
| Weight Per each | 15 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-----------------------|---|
| Application | For Cable And Wire Junction, Distribution And Termination, Houses Runs Of Control And Power Cable |
| Enclosure standard | NEMA 1, IP30 C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC 60529, RoHS Compliant |