



## 6644CHC Encl 6X6X4 N4 CH Clamp CVR

Cooper B-Line/Cable Tray

Catalog Number	6644CHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 6" Height, 4" Length, 6" Width, Nema 4, Hinged Cover, 4CHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	3.9 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

### Features

dimensions	4.0000 IN X 6.0000 IN X 6.0000 IN
Mounting Type	Wall

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	6.00 In Width X 4.00 In Depth X 6.00 In Height
------	--

### Descriptions

Description	ENCL 6X6X4 N4 CH CLAMP CVR
extra long description	B-LINE 664-4CHC TYPE 4 JIC CONTINUO
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 6" height, 4" length, 6" width, NEMA 4, Hinged cover, 4CHC enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 4 Jic Continuous Hinge CVR Enc, 6X6X4
Special Features	Cont. piano hinge with s.s. door clamp,panel mount

### Manufacturer Information

Brand	Eaton
GTIN	00782051740202
Manufacturers Part Number	664-4CHC
UPC	782051740202

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	3.9

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Lighting and Lighting Controls Ind Facilities & Factories - Industrial Facilities/Factories - Other Ind Facilities & Factories - Facility: Safety and Security Systems Ind Facilities & Factories - Facility: Critical Power Ind Facilities & Factories - Mfg. Process Electrification and Control Ind Facilities & Factories - Facility: Power Distribution and Control Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Commercial / Institutional Building
Mounting	EXTERNAL FEET, WALL
nema rating	4
standard	CSA C22.2.,NEMA,UL 50