



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



664WG SW 4W Ac 15A 120V GRD Terminals WH

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 664WG |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Grounding Toggle Switch, 4 Poles, 4 Ways, 15 A, 120 V, Thermoplastic, White, Wall Mount, 1.25 (L) X 1.090 (W) X 3.281 (H) In, 0.21 LB |
| Weight per unit | 0.2072 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|---------------------|
| amperage rating | 15 |
| connection | Grounding |
| Contact Rating | 15 Amp, 120/125 VAC |
| media | Yes |
| Number of Wires | 3 |
| Poles | 4-Way |
| Voltage | 120.0 V |
| Voltage Rating | 120 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | SW 4W AC 15A 120V GRD TERMINALS WH |
| extra long description | P&S 664WG SW 4W AC 15A 120V GRD TER |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007664027 |
| Manufacturers Part Number | 664WG |
| UPC | 785007664027 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential Switches |
| Type | Grounding Toggle Switch |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.2072 |

Uses, Certifications, and Standards

| | |
|----------|------------------------|
| Mounting | WALL |
| standard | CULUS, UL, CSA, UL 498 |