



Catalog Number: 666-SC1  
Item Description: N1 SCREW COVER ENCL  
UPC Code: 784572108189




Brand Name: Milbank  
Type: Screw Cover  
Special Features: Cover Secured with Plated Screws  
Application: Enclosure for Mounting Electrical Equipment  
Standard: UL Listed  
Number Of Outlet: 0  
Material: Steel with Powder Coat Finish  
Color: ANSI 61 Gray  
Mounting: Wall Mount  
NEMA Rating: Type 1



*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

| CATALOG#   | LABEL#  |
|------------|---------|
| 666-SC1    | 1002135 |
| RC-666-SC1 | 1125021 |
| SPSC-666   | 1132714 |
| SPSC-666N  | 1132714 |

| ITEM | QTY.  | PART NUMBER | DESCRIPTION              |
|------|-------|-------------|--------------------------|
| 1    | 1     | (SEE CHART) | BACK WELDMENT            |
| 2    | 1     | (SEE CHART) | COVER PLATE              |
| 3    | 1     | 1002170     | BAG ASS'Y (SEE NOTE)     |
| 4    | 1     | (SEE CHART) | U/L LISTING LABEL        |
| 5    | 1     | 1002475     | BAG ASSY (GROUND SCREW)  |
| 6    | 0.166 | 1002133     | CARTON 6-PER (NOT SHOWN) |





| SUFFIX | FINISH             | WELDMENT NO. | PLATE NO. | INSTALL KOs |
|--------|--------------------|--------------|-----------|-------------|
| NONE   | MILBANK LIGHT GRAY | 1161975      | 1156568   | YES         |
| -NP    | NONE               | 1161977      | 1003322   |             |
| -NK    | MILBANK LIGHT GRAY | 1161976      | 1156568   | NO          |
| -NK-NP | NONE               | 1161978      | 1003322   |             |

NOTES:

1. PLACE BAG ASS'Y INSIDE ENCLOSURE (NOT SHOWN).

NEMA DWG.: #124

|  |                    |  |   |  |
|--|--------------------|--|---|--|
| Material:  | 16 GA. GALV. STEEL |  |  General Offices:<br>Kansas City, MO |  |
| Finish:  | SEE CHART          |  |   |  |
| Tolerances:<br>Unless Specified Otherwise<br>X.X ±.1<br>X.XX ±.03<br>X.XXX ±.015<br>X° ±2° |                    | Third Angle<br> | Title:  | 666<br>SCREW COVER<br>TYPE 1 ENCLOSURE |
|  |                    | Projection   | Catalog No.:  | (SEE CHART)                            |
|  |                    |  | Customer:   | MILBANK STANDARD                       |
|  |                    |  | Drawing No.:  | <b>1003060</b>                         |
| Scale:   | NTS                | Checked By:  | Date:   | 04/26/01                               |
| Drawn By:  | DY                 | Approved By:   | Sheet   | 1 of 1                                 |

|    |          |                             |    |  |  |  |
|----|----------|-----------------------------|----|--|--|--|
| D4 | 11/20/12 | CHART VERSIONS (ECO #23228) | DF |  |  |  |
|----|----------|-----------------------------|----|--|--|--|



Catalog Number: 666-SC1  
Item Description: N1 SCREW COVER ENCL  
UPC Code: 784572108189




Brand Name: Milbank  
Type: Screw Cover  
Special Features: Cover Secured with Plated Screws  
Application: Enclosure for Mounting Electrical Equipment  
Standard: UL Listed  
Number Of Outlet: 0  
Material: Steel with Powder Coat Finish  
Color: ANSI 61 Gray  
Mounting: Wall Mount  
NEMA Rating: Type 1



*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

| CATALOG#   | LABEL#  |
|------------|---------|
| 666-SC1    | 1002135 |
| RC-666-SC1 | 1125021 |
| SPSC-666   | 1132714 |
| SPSC-666N  | 1132714 |

| ITEM | QTY.  | PART NUMBER | DESCRIPTION              |
|------|-------|-------------|--------------------------|
| 1    | 1     | (SEE CHART) | BACK WELDMENT            |
| 2    | 1     | (SEE CHART) | COVER PLATE              |
| 3    | 1     | 1002170     | BAG ASS'Y (SEE NOTE)     |
| 4    | 1     | (SEE CHART) | U/L LISTING LABEL        |
| 5    | 1     | 1002475     | BAG ASSY (GROUND SCREW)  |
| 6    | 0.166 | 1002133     | CARTON 6-PER (NOT SHOWN) |





| SUFFIX | FINISH             | WELDMNT NO. | PLATE NO. | INSTALL KOs |
|--------|--------------------|-------------|-----------|-------------|
| NONE   | MILBANK LIGHT GRAY | 1161975     | 1156568   | YES         |
| -NP    | NONE               | 1161977     | 1003322   |             |
| -NK    | MILBANK LIGHT GRAY | 1161976     | 1156568   | NO          |
| -NK-NP | NONE               | 1161978     | 1003322   |             |

NOTES:

1. PLACE BAG ASS'Y INSIDE ENCLOSURE (NOT SHOWN).

NEMA DWG.: #124

|    |          |                             |    |  |  |  |  |  |  |           |     |              |  |              |                       |
|----|----------|-----------------------------|----|--|--|--|--|--|--|-----------|-----|--------------|--|--------------|-----------------------|
| D4 | 11/20/12 | CHART VERSIONS (ECO #23228) | DF |  |  |  |  |  |  | Scale:    | NTS | Checked By:  |  | Drawing No.: | <b>1003060</b>        |
|    |          |                             |    |  |  |  |  |  |  | Drawn By: | DY  | Approved By: |  | Date:        | 04/26/01 Sheet 1 of 1 |

|  |                    |   |  |
|--|--------------------|---|--|
| Material:  | 16 GA. GALV. STEEL |  General Offices:<br>Kansas City, MO |  |
| Finish:  | SEE CHART          |   |  |
| Tolerances:<br>Unless Specified Otherwise<br>X.X ±.1<br>X.XX ±.03<br>X.XXX ±.015<br>X° ±2° |                    | Title:  | 666<br>SCREW COVER<br>TYPE 1 ENCLOSURE |
|       |                    | Catalog No.:  | (SEE CHART)                            |
|  |                    | Customer:   | MILBANK STANDARD                       |
|  |                    | Drawing No.:  | <b>1003060</b>                         |
|  |                    | Date:   | 04/26/01                               |
|  |                    | Sheet   | 1 of 1                                 |