


MODEL 682
DUCTLESS CEILING/WALL FAN



Processes air to eliminate odors where ductwork is impossible.

FEATURES

GRILLE:

- Attractive, self-adjusting grille conceals fan interior
- White, polymeric - blends well with any decor
- Torsion spring grille mounting - no tools required

MOTOR:

- Plug-in, removable motor assembly
- Polymeric impeller

HOUSING:

- Patented snap-in mounting saves time and money
- Mounts easily to framing
- Long-lasting activated charcoal filter - easy to replace

Controls designed for use with these products (purchase separately):

- Model 57V (Ivory) / 57W (White) Electronic Variable Speed Control - 3 amp
- Model 69V (Ivory) / 69W (White) Single-Function Control

SPECIFICATIONS

| MODEL | VOLTS | AMPS |
|-------|-------|------|
| 682 | 120 | 1.0 |



TYPICAL SPECIFICATION


Ventilator shall be Broan Model 682.

Unit shall have steel housing with snap-in mounting system.

Fan to have activated charcoal filter. Motor assembly shall be removable for cleaning and service.

Grille to be self-adjusting and require no tools to install or remove.


Unit shall be U.L. Listed.



Broan-NuTone LLC Hartford, Wisconsin www.broan.com 800-558-1711

| REFERENCE | QTY. | REMARKS | Project | |
|-----------|------|---------|--------------|------|
| | | | Location | |
| | | | Architect | |
| | | | Engineer | |
| | | | Contractor | |
| | | | Submitted by | Date |

**MODEL 682
DUCTLESS CEILING/WALL FAN**



Processes air to eliminate odors where ductwork is impossible.

FEATURES

GRILLE:

- Attractive, self-adjusting grille conceals fan interior
- White, polymeric - blends well with any decor
- Torsion spring grille mounting - no tools required

MOTOR:

- Plug-in, removable motor assembly
- Polymeric impeller

HOUSING:

- Patented snap-in mounting saves time and money
- Mounts easily to framing
- Long-lasting activated charcoal filter - easy to replace

Controls designed for use with these products (purchase separately):

- Model 57V (Ivory) / 57W (White) Electronic Variable Speed Control - 3 amp
- Model 69V (Ivory) / 69W (White) Single-Function Control

SPECIFICATIONS

| MODEL | VOLTS | AMPS |
|-------|-------|------|
| 682 | 120 | 1.0 |



TYPICAL SPECIFICATION


Ventilator shall be Broan Model 682.

Unit shall have steel housing with snap-in mounting system.

Fan to have activated charcoal filter. Motor assembly shall be removable for cleaning and service.

Grille to be self-adjusting and require no tools to install or remove.

Unit shall be U.L. Listed.



Broan-NuTone LLC Hartford, Wisconsin www.broan.com 800-558-1711

| REFERENCE | QTY. | REMARKS | Project | |
|-----------|------|---------|--------------|------|
| | | | Location | |
| | | | Architect | |
| | | | Engineer | |
| | | | Contractor | |
| | | | Submitted by | Date |