



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



690W Single Pole, Double Switch, 15A, 120/277V, White *Pass & Seymour/Legrand*

| | |
|------------------|--|
| Catalog Number | 690W |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Single Pole, Double Switch, 15 Amps, 120/277 Volts, White. |
| Weight per unit | 0.2100 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|-----------------|---------------|
| amperage rating | 15 |
| connection | Non Ground |
| Material | Thermoplastic |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage Rating | 120/277 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | White |
|-------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Description | SINGLE POLE, DOUBLE SWITCH, 15A, 120/277V, WHITE |
| extra long description | P&S 690W COMBO 2SWITCHES 1POLE 15A1 |
| Long Description | Single Pole, Double Switch, 15 amps, 120/277 volts, White. |
| Product Type | Combo 2SWITCHES 1POLE 15A120/277V W |
| Special Features | Two devices fits in one space, side wire |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007690125 |
| Manufacturers Part Number | 690W |
| UPC | 785007690125 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | Combination switch |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.21 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| nema rating | 5-15R |
| standard | UL 498 |