



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main  
75652-4459, TX Henderson  
Phone: 903-657-1517  
Fax: 903-657-0253



## 691W Combo 15A 1 SW 1P-120V 1RECP-125V WH

*Pass & Seymour/Legrand*

Catalog Number	691W
Manufacturer	Pass & Seymour/Legrand
Description	Combination Switch, 1 Pole, 15 A, 120/125 V, White, 3 Wires, Thermoplastic, 1.32 (L) X 0.94 (W) X 3.28 (H) In, Toggle Actuator, Wall Mount, 0.22 LB
Weight per unit	0.2171 (lbs/each)
Product Category	Combination Devices

### Features

actuator	Toggle
amperage rating	15
connection	Side wire
Connection Type	Wired
Contact Rating	15 Amp, 120/125 VAC
indoor/outdoor	Indoor
Load Rating	15 A @ 120/125 VAC
Load Type	Fluorescent, CFL, Halogen, Xenon, Universal, Incandescent, LED
Number of Gangs	1
Number of Switches	1.0
operating cycles	3000
Outlet Type	Indoor
Poles	1
supply voltage	120.0
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 125 VAC
Wall Plate Included	NO
Wire Size	4

### Material, Color, and Finish

Finish	SATIN
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	COMBO 15A 1 SW 1P-120V 1RECP-125V WH
extra long description	P&S 691W COMBO 15A 1 SW 1P-120V 1RE
Special Features	Two devices fits in one space, side wire



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main  
75652-4459, TX Henderson  
Phone: 903-657-1517  
Fax: 903-657-0253

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007691023
Manufacturers Part Number	691W
UPC	785007691023

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet, Switch, Combination

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.2171

## Uses, Certifications, and Standards

environmental conditions	Flammability: UL94 V2
Mounting	WALL
standard	CULUS, UL 498