



## NON-GROUNDING COMBINATION SWITCHES

693LA | [Pass & Seymour](#)

### FEATURES & BENEFITS

Double Three-way Combination Switch, 15 amps, 120/277 volts, Light Almond.



- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Type: Combination, Double  
Number Of Poles: 3-way  
Special Features: Non-Grounding

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121406

## DIMENSIONS

Depth (US): 0.94"

Height (US): 3.28"

Width (US): 1.32"

## TECHNICAL INFORMATION

Amps: 16A

Volts: 120/277VAC

Volts (AC): 120/277

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





## NON-GROUNDING COMBINATION SWITCHES

693LA | [Pass & Seymour](#)

### FEATURES & BENEFITS

Double Three-way Combination Switch, 15 amps, 120/277 volts, Light Almond.



- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Type: Combination, Double  
Number Of Poles: 3-way  
Special Features: Non-Grounding

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121406

## DIMENSIONS

Depth (US): 0.94"

Height (US): 3.28"

Width (US): 1.32"

## TECHNICAL INFORMATION

Amps: 16A

Volts: 120/277VAC

Volts (AC): 120/277

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

