



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



693LAG Combo 2 Switches 3W 15A 120/277V La

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 693LAG |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Double 3-Way Combination Switch, 15A, 120/277V |
| Weight per unit | 0.2675 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|-----------------------|--|
| action | (2) 3W |
| actuator | Toggle |
| amperage rating | 15 |
| connection | Side wire |
| Contact Configuration | N-O |
| Contact Rating | 15amp, 120/277vac |
| operating cycles | 30k.0 |
| Poles | 3-way |
| Voltage | 120/277 V |
| Voltage Rating | 0.433212996389892 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|--------------------------|
| Size | 1.32 L x 0.94 W x 4.06 H |
|------|--------------------------|

Descriptions

| | |
|------------------------|---|
| Description | COMBO 2 SWITCHES 3W 15A 120/277V LA |
| extra long description | P&S 693LAG COMBO 2 SWITCHES 3W 15A |
| Features | Combination |
| Long Description | Double 3-way Combination Switch, 15A, 120/277V |
| Product Type | Combo 2 Switches 3W 15A 120/277V La |
| Special Features | Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements. |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007006148 |
| Manufacturers Part Number | 693-LAG |
| UPC | 785007006148 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | COMBINATION |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 20 |
| Weight Per each | 0.2675 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Residential/Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| Operating Temperature | Maximum continuous +60°C, minimum -30°C |
| standard | CULUS, UL20 |