



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



701S Dual Purpose Hacksaw 3 In 1 Blade

Klein Tools

Catalog Number	701S
Manufacturer	Klein Tools
Description	This Versatile Hack Saw Blade Has Three Teeth Sizes and The Ability to Quickly Convert The Blade to 90 or 45 Degrees For Standard or Flush-Cut Applications. The Pivot-Lock Adjusts Blade Tension For Straighter Cuts and Longer Blade Life. It Also Features A Set Screw Which Allows For Storage Of Extra Blades and Secures Blade For "Jab" Sawing.
Weight per unit	1.5 (lbs/each)
Product Category	Tools & Testers

Features

Blade Length	12" (30.5 cm)
media	Yes
Overall Height	1" (2.5 cm)
Overall Width	1" (2.5 cm)

Material, Color, and Finish

Blade Material	Steel
----------------	-------

Dimensions and Weight

Overall Length	16" (40.6 cm)
----------------	---------------

Descriptions

Description	DUAL PURPOSE HACKSAW 3 IN 1 BLADE
extra long description	KLEIN 701-S Dual Purpose Hacksaw 3
Long Description	This versatile hack saw blade has three teeth sizes and the ability to quickly convert the blade to 90 or 45 degrees for standard or flush-cut applications. The Pivot-lock adjusts blade tension for straighter cuts and longer blade life. It also features a set screw which allows for storage of extra blades and secures blade for "jab" sawing.
Product Type	Dual Purpose Hacksaw 3 In 1 Blade
Special Features	Blade with Three Teeth Sizes Converts to 90° or 45°

Manufacturer Information

Brand	Klein Tools
GTIN	00092644313066
Manufacturers Part Number	701-S
UPC	092644313066



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description BITS, BLADES, AND HOLE SAWS
Type Dual Purpose Hacksaw

Availability

Status Inactive

Packaging

Carton 1
Package 6
Weight 1.5 lb (0.7 kg)
Weight Per each 1.45

Uses, Certifications, and Standards

Application Standard and Flush-Cut Applications
standard —