



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7030BSL 120V Ac Smoke & Carbon Monoxide Alarm With Led STR

BRK Brands/Ademco/First Alert

Catalog Number	7030BSL
Manufacturer	BRK Brands/Ademco/First Alert
Description	Hardwired Combo Smoke & CO Alarm With 10-Year Sealed Lithium Battery Backup. Includes 177 Candela Led Strobe Light. Ac 120V Interconnectable With Silence and Latching Features. Includes Photoelectric Smoke Sensing Technology and Electrochemical Carbon Monoxide Sensor.
Weight per unit	0.8720 (lbs/each)
Product Category	Builders Products

Features

alarm type	Audio
dimensions	5.6" diameter x 2.0" height
Operating Voltage	120V AC 60Hz with 10-Year Sealed Lithium Battery Backup
Output Current	10-Year Sealed Lithium Battery
Sensor Type	Photo / Electrochemical
Temperature Range	40 Degree F (4 Degree C) to 100 Degree F (38 Degree C)

Material, Color, and Finish

Color	White
Enclosure Material	Plastic

Descriptions

Description	120V AC SMOKE & CARBON MONOXIDE ALARM WITH LED STR
extra long description	BRK 1038870 ALRM 3IN1 7030BSL SMK-C
Features	Hardwired Combo smoke & CO alarm with 10-Year sealed lithium battery backup. Includes 177 candela LED Strobe light.
Long Description	Hardwired Combo smoke & CO alarm with 10-Year sealed lithium battery backup. Includes 177 candela LED Strobe light. AC 120V Interconnectable with Silence and Latching features. Includes Photoelectric smoke sensing technology and electrochemical carbon monoxide sensor.
Product Type	Alrm 3IN1 7030BSL SMK-CO-Strbe Ac/DC 10y

Manufacturer Information

Brand	BRK
GTIN	00029054018137
Manufacturers Part Number	1038870
UPC	029054018137



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	SMOKE DETECTORS
Type	Combination Strobe, Smoke & Carbon Monoxide Alarm

Packaging

Carton	1
Package	6
Weight Per each	0.872

Uses, Certifications, and Standards

Application	Single and or multiple station strobe alarm specifically designed to detect smoke and carbon monoxide in residential and institutional applications including sleeping rooms of hospitals, hotels, motels, dormitories and other multi-family dwellings.
environmental conditions	10 percent to 90 percent relative humidity (RH)
Mounting	mounts to wall or ceiling
standard	UL217, UL2034