



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7075ST 3/4 In Emt Comp Conn Insul Steel *Appleton/Oz Gedney*

Catalog Number	7075ST
Manufacturer	Appleton/Oz Gedney
Description	Features:1 1/32IN Dia X 1 1/4IN Length, 7/16 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:0.75IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated, Insulation:Insulated Throat, Temperature Rating:90ce
Weight per unit	0.1800 (lbs/each)
Product Category	Steel Insulated Straight Compr

### Features

connection	Male NPS Thread
Connector Type	Compression
insulation	Insulated Throat
Material	Steel

### Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

### Dimensions and Weight

Size	0.75
------	------

### Descriptions

Description	3/4 IN EMT COMP CONN INSUL STEEL
extra long description	EGS 7075ST 3/4 IN EMT COMP CONN INS
Long Description	Features:1 1/32IN Dia X 1 1/4IN Length, 7/16 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:0.75IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated,Insulation:Insulated Throat, Temperature Rating:90CE
Product Type	3/4 In Emt Comp Conn Insul Steel
Special Features	1 1/32 IN Dia X 1 1/4 IN Length, 7/16 IN Thread Length, Concretetight

### Manufacturer Information

Brand	APPOZGCOMM
GTIN	00687855873142
Manufacturers Part Number	7075ST
UPC	687855873142



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	EMT Conduit Straight Compression Connector

## Trade Size

Trade Size	0.75
------------	------

## Packaging

Carton	25
Package	250
Weight Per each	0.18

## Uses, Certifications, and Standards

Application	To ground and secure EMT Raceways to boxes and enclosures
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: C22.2 No. 18.3, cUL Listed: E14815; CSA Certified: 028507; NEMA: FB-1
Temperature Rating	90