



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7240V Double MC Connector *Appleton/Oz Gedney*

Catalog Number	7240V
Manufacturer	Appleton/Oz Gedney
Description	Conduit Connector, Size: 3/8 In, Connection: Armored Cable X Flexible Metal Conduit, Conductor Range: 0.34 - 0.63 In, Material: Malleable Iron, Finish: Zinc Electroplate, Length: 0.97 In, Width: 1-3/4 In, Thread Length: 0.47 In, Knockout Si
Weight per unit	0.1500 (lbs/each)
Product Category	Liquid Tight Fittings

Features

connection	Armored Cable X Flexible Metal Conduit
Material	Malleable Iron

Material, Color, and Finish

Finish	Zinc Electroplate
--------	-------------------

Dimensions and Weight

Size	3/8
------	-----

Descriptions

Description	DOUBLE MC CONNECTOR
extra long description	APP 7240V 3/8-1/2 IN DUPLEX BOX CON
Long Description	Conduit Connector, Size: 3/8 IN, Connection: Armored Cable X Flexible Metal Conduit, Conductor Range: 0.34 - 0.63 IN, Material: Malleable Iron, Finish: Zinc Electroplate, Length: 0.97 IN, Width: 1-3/4 IN, Thread Length: 0.47 IN, Knockout Si
Product Type	3/8-1/2 In Duplex Box Conn
Special Features	Furnished with locknut; Male hub threads-NPS

Manufacturer Information

Brand	Appleton
GTIN	00781381772556
Manufacturers Part Number	7240V
UPC	781381772556

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONDUIT CONNECTOR

Packaging

Carton	1
Weight Per each	0.15



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Used To Ground And Secure Nonmetallic Sheathed And
Service Entrance Cable to Boxes And Enclosures

standard

UL 514B, UL Listed: E14813, CSA Standard: C22.2 No. 18.3, CSA
Certified: 065178, NEMA FB-1