



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 75454 Stinger DS Led HL Flashlight *Streamlight, Inc.*

Catalog Number	75454
Manufacturer	Streamlight, Inc.
Description	Stinger, Rechargeable Nimh Battery Battery Type, 800 LM Brightness (Lumens), Anodized Finish, 22.48 CM;8.85 In Length, Aluminum Material, IEC Type A Standards Met, 12 V DC;120 V Voltage Rating, 12.8 Oz;364 G Weight
Weight per unit	2.9 (lbs/each)
Product Category	Misc

### Features

Battery Included	Yes
Battery Size	Nickel-Metal Hydride
Lamp Type	LED
Number of Batteries	1

### Material, Color, and Finish

Body Material	Aluminum
Color	Black

### Descriptions

Additional Information	Intensity 800 Lumen; Run Time 5 Hour (Low), 1.5 Hour (High); Beam Distance 310 Meter; Maximum Candela 24000; Includes 120 Volt AC/12 Volt DC Cord
Commodity Description	FLASHLIGHTS,LANTERNS,WARNING LIGHTS
Description	STINGER DS LED HL FLASHLIGHT
extra long description	RECHARGEABLE TYPE; BLACK COLOR; CE APPROVAL; ALUMINUM BODY MATERIAL; LED LAMP TYPE; NICKEL-METAL HYDRIDE BATTERY SIZE; 1 BATTERY(S); YES BATTERY INCLUDED; STINGER DS[R] BRAND; INTENSITY 800 LUMEN; RUN TIME 5 HOUR (LOW), 1.5 HOUR (HIGH); BEAM DISTANCE 310 METER; MAXIMUM CANDELA 24000; INCLUDES 120 VOLT AC/12 VOLT DC CORD

### Manufacturer Information

Brand	Streamlight, Inc.
GTIN	00080926754546
UPC	080926754546

### Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	Rechargeable



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	6
Weight Per each	2.9033

## Uses, Certifications, and Standards

Approval	CE
----------	----