



**Product Number:** 16751

**Order Abbreviation:** 80PAR38/HAL/S/WFL50 120V

**General Description:** Tungsten Halogen PAR38 Reflector Lamp 80Watt 120Volt Medium Skirted Base WideFlood50 Beam

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	80PAR38HALSWFL50 120V 10/CS 1/SKU
Approx. Lumens	1545
Average Rated Life (hr)	1500
Base	E26 Medium Skirted
Beam Angle (deg)	50
Beam Type	WFL
Bulb	PAR38
Centerbeam Candlepower (cp)	2300
Class	YES
Color Rendering Index (CRI)	99
Color Temperature/CCT (K)	2950
Diameter (in)	4.752
Diameter (mm)	120.70
Family Brand Name	CAPSYLITE® PAR38
Filament	CC-8
Horizontal Beam Angle (deg)	50
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	5.313
Maximum Overall Length - MOL (mm)	134.9375
Nominal Voltage (V)	120.00
Nominal Wattage (W)	80.00
Vertical Beam Angle (deg)	50



#### Footnotes

- State of the Art SPL Optics
- To avoid electric shock and/or skin burns, turn off power and allow bulb to cool before handling or attempting replacement.
- In base up operation, heat may eventually deteriorate paper-lined or plastic sockets.



**Product Number:** 16751

**Order Abbreviation:** 80PAR38/HAL/S/WFL50 120V

**General Description:** Tungsten Halogen PAR38 Reflector Lamp 80Watt 120Volt Medium Skirted Base WideFlood50 Beam

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	80PAR38HALSWFL50 120V 10/CS 1/SKU
Approx. Lumens	1545
Average Rated Life (hr)	1500
Base	E26 Medium Skirted
Beam Angle (deg)	50
Beam Type	WFL
Bulb	PAR38
Centerbeam Candlepower (cp)	2300
Class	YES
Color Rendering Index (CRI)	99
Color Temperature/CCT (K)	2950
Diameter (in)	4.752
Diameter (mm)	120.70
Family Brand Name	CAPSYLITE® PAR38
Filament	CC-8
Horizontal Beam Angle (deg)	50
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	5.313
Maximum Overall Length - MOL (mm)	134.9375
Nominal Voltage (V)	120.00
Nominal Wattage (W)	80.00
Vertical Beam Angle (deg)	50



#### Footnotes

- State of the Art SPL Optics
- To avoid electric shock and/or skin burns, turn off power and allow bulb to cool before handling or attempting replacement.
- In base up operation, heat may eventually deteriorate paper-lined or plastic sockets.