



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 839511 Vinyl Insul Feml Disconn 22-18AWG, .110", 25/Box

*Ideal*

Catalog Number	839511
Manufacturer	Ideal
Description	Ideal, Disconnect Terminal, Vinyl Insulated, Wire Size: 22 - 18 Awg, Voltage Rating: 300 V, Material: Brass, Finish: Tin-Plated, Insulation: 0.150 In Diameter, Connection: Female, Tab Size: 0.110 In X 020 In, Temperature Rating: 75 Deg C
Weight per unit	0.0040 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Female
insulation	0.150 IN Diameter
Material	Brass
Voltage Rating	300
Wire Size	22 - 18

### Material, Color, and Finish

Finish	Tin-Plated
--------	------------

### Descriptions

Description	VINYL INSUL FEML DISCONN 22-18AWG, .110", 25/BOX
extra long description	IDEAL 83-9511 TRM QCK DISC VINL22-1
Features	Butted seam-construction prevents splitting under maximum pressureInternal barrel serrations grip wires tightly to resist pull-out and reduce electrical resistanceTin-plated brass construction for corrosion resistanceShouldered barrel insulation quickly positions terminal for proper crimpingExpanded insulation entry accommodates a wide variety of insulation diameters and provides additional insulation supportThe complete line of IDEAL crimp terminals, disconnects, and splices offer the right product for an
Long Description	IDEAL, Disconnect Terminal, Vinyl Insulated, Wire Size: 22 - 18 AWG, Voltage Rating: 300 V, Material: Brass, Finish: Tin-Plated, Insulation: 0.150 IN Diameter, Connection: Female, Tab Size: 0.110 IN X 020 IN, Temperature Rating: 75 DEG C
Product Type	TRM QCK Disc VINL22-18AWG-25PK
Special Features	Features: Tin-Plated Brass Construction For Corrosion Resistance; Brazed Or Butted Seams Prevent Splitting; Funnel Entry Insulators; Beveled Barrel Openings Provide Easy Wire Entry; Clearly Marked Wire And Stud Ranges; Color-Coded Insulation; Tab Size: 0.110 IN X 020 IN; Temperature Rating: 75 DEG C



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Ideal
GTIN	00783250490585
Manufacturers Part Number	839511
UPC	783250490585

## Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Vinyl Insulated

## Availability

minimum qty	25
-------------	----

## Packaging

Carton	25
Weight Per each	0.004

## Uses, Certifications, and Standards

standard	CUL Listed, RoHS
----------	------------------