

# Compression Connectors



## **RTQ™ Reg/Tri/Quad & Plenum F-Connectors**

- Fits 60% regular, tri-shield and quad shield cables
- Nickel-plated, brass-construction for superior corrosion resistance
- Designed for use in satellite and cable TV installations
- WeatherProof™ for indoor and outdoor use
- Use 30-603, 30-793 or LinearX Compression Tools

## **RG-11 F-Connectors**

- Fits 60% regular RG-11 cable
- Nickel-plated, brass-construction for superior corrosion resistance
- Designed for use in satellite and cable TV installations
- WeatherProof™ for indoor and outdoor use
- Use 30-603 or 30-793 Compression Tools
- Use 45-111, 1/4" x 1/4" RG-11 Coax Stripper




## **BNC Connectors**

- Nickel-plated, brass-construction for superior corrosion resistance
- Moisture-inhibiting design
- Use 30-793 Compression Tool
- 75 Ohm nominal impedance
- Gold-plated pin contact area
- Available in plenum versions


## **OmniCONN™ F-Connectors**

- Non corrosive nickel plated brass body and polycarbonate bushing
- Delrin/Nylon adapter sleeve and o-ring provide double protection for a watertight seal
- Free spinning hex nut for ease of installation onto all 7/16 ports
- 75 ohm nominal impedance
- Two-piece pre-assembled connectors



## **RCA Connectors**

- Constructed of nickel plated brass and gold plated head
- 75 ohm nominal impedance
- Bandwidth up to 3 GHz
- Compatible with 30-603 and 30-793 Compression Tools



## Compression Connectors

	Connector Type	Cable Type	Qty.	Cat. No.
	F	RG-6 Reg/Tri/Quad	Card of 4	<b>92-654</b>
			Card of 10	<b>92-651</b>
			Jar of 50	<b>92-650</b>
			Jar of 100	<b>92-656</b>
			Box of 1,000 bulk	<b>92-659</b>
	F	RG-6 Quad	Jar of 50	<b>92-655</b>
	F	RG-6 Plenum	Jar of 50	<b>92-660</b>
	F	RG-59 Reg/Tri/Quad	Card of 10	<b>92-611</b>
			Jar of 50	<b>92-610</b>
	F	RG-11 Plenum	Card of 10	<b>92-212</b>
	F	RG-11	Card of 10	<b>89-211</b>
			Box of 500	<b>89-1211</b>
	F	RG-6	Jar of 50	<b>89-044</b>
	F	RG-6 Quad	Jar of 50	<b>89-045</b>
	BNC	RG-6	Card of 4	<b>92-705</b>
			Card of 15	<b>89-048</b>
			Jar of 35	<b>89-5048</b>
	BNC	RG-6 Plenum	Card of 15	<b>89-050</b>
			Jar of 35	<b>89-5050</b>
	BNC	RG-59	Card of 4	<b>92-704</b>
			Card of 15	<b>89-047</b>
			Jar of 35	<b>89-5047</b>
			Box of 1,000 (10 bags, 100 ea.)	<b>89-1047</b>
	BNC	RG-59 Plenum	Card of 15	<b>89-049</b>
			Jar of 35	<b>89-5049</b>
	RCA*	RG-6	Card of 4	<b>92-582</b>
			Card of 10	<b>89-582</b>
			Jar of 35	<b>89-580</b>
	RCA*	RG-59	Card of 4	<b>92-572</b>
			Jar of 35	<b>89-570</b>

\*RCA Connectors include an assortment of color ID bands.

## Compression Port Seals – 1/2 in.

- Used with compression F-connectors to weatherproof connectors by placing onto the female port. Made from EPDM for superior sealing.



Description	Qty.	Cat. No.
Long Sleeve Compression F-Connector Port Seals, 1/2 in.	Bag of 100	<b>89-127</b>