



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 9125 Tape Measure, 25-Foot Single-Hook

*Klein Tools*

Catalog Number	9125
Manufacturer	Klein Tools
Description	Klein Tools Measuring Tapes Deliver Performance and Durability Expected By Professional Tradespeople. Safeguarded By A Thick and Durable Protective Nylon-Coating, The Tough Blade Stands Out to 13-Foot With A 16-Foot Reach. Able to Endure The Toughest Of Jobsite Conditions, This Tool Also Features A Single Hook, Easy-to-Read Bold Lines, and A Retraction Brake.
Weight per unit	1.3 (lbs/each)
Product Category	Miscellaneous Hand Tools

### Features

Belt Clip	Yes
graduations	1/16"
Material	Plastic Case with Steel Blade
media	Yes
Overall Height	3.43" (8.7 cm)
Overall Width	2.35" (6 cm)
Tape Length	25' (7.6 m)

### Material, Color, and Finish

Case Color	Orange/Black
Case Material	PC-ABS with TPR Overmolding
Tape Material	STEEL

### Dimensions and Weight

Overall Length	3.43" (8.7 cm)
----------------	----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	TAPE MEASURE, 25-FOOT SINGLE-HOOK
extra long description	KLEIN 9125 25 Foot Non-Magnetic Tap
Features	Klein Tools Measuring Tapes deliver performance and durability expected by professional tradespeople. Safeguarded by a thick and durable protective nylon-coating, the Tough Blade stands out to 13-Foot with a 16-Foot Reach. Able to endure the toughest of jobsite conditions, this tool also features a single hook, easy-to-read bold lines, and a retraction brake.
Long Description	Klein Tools Measuring Tapes deliver performance and durability expected by professional tradespeople. Safeguarded by a thick and durable protective nylon-coating, the Tough Blade stands out to 13-Foot with a 16-Foot Reach. Able to endure the toughest of jobsite conditions, this tool also features a single hook, easy-to-read bold lines, and a retraction brake.
Product Type	25 Foot Non-Magnetic Tape Measure
Special Features	16-Foot Reach;Attachment Channel to Tether Tape Measure;Easy-to-read Bold Lines Every 1/8-Inch;Tough Blade

## Manufacturer Information

Brand	Klein Tools
GTIN	00092644692673
Manufacturers Part Number	9125
UPC	092644692673

## Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Closed Case, Double Sided Single Non-Magnetic Hook

## Packaging

Carton	1
Package	6
Weight	20.7
Weight Per each	1.29

## Uses, Certifications, and Standards

Application	Linear Measurement
-------------	--------------------