



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 9216 Tape Measure, 16-Foot Magnetic Double-Hook

*Klein Tools*

|                  |  |
|------------------|--|
| Catalog Number   | 9216   |
| Manufacturer     | Klein Tools  |
| Description      | Klein Tools Tape Measures Deliver Performance and Durability Expected By Professional Tradespeople. Safeguarded By A Thick and Durable Protective Nylon-Coating, The Tough Blade Has A 16-Foot Reach. Able to Endure The Toughest Of Jobsite Conditions, This Tool Also Features A Strong Magnetic Double Hook, Easy-to-Read Bold Lines, and A Retraction Brake. |
| Weight per unit  | 0.9200 (lbs/each)  |
| Product Category | Miscellaneous Hand Tools   |

### Features

|                |                               |
|----------------|-------------------------------|
| Belt Clip      | Yes                           |
| graduations    | 1/16"                         |
| Material       | Plastic Case with Steel Blade |
| media          | Yes                           |
| Overall Height | 3.01" (7.5 cm)                |
| Overall Width  | 2.35" (6 cm)                  |
| Tape Length    | 16' (4.9 m)                   |

### Material, Color, and Finish

|               |                             |
|---------------|-----------------------------|
| Case Color    | Orange/Black                |
| Case Material | PC-ABS with TPR Overmolding |
| Tape Material | STEEL                       |

### Dimensions and Weight

|                |              |
|----------------|--------------|
| Overall Length | 3.07" (8 cm) |
|----------------|--------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | TAPE MEASURE, 16-FOOT MAGNETIC DOUBLE-HOOK   |
| extra long description | KLEIN 9216 16' Double Hook Tape Mea  |
| Features               | Klein Tools Tape Measures deliver performance and durability expected by professional tradespeople. Safeguarded by a thick and durable protective nylon-coating, the Tough Blade has a 16-Foot reach. Able to endure the toughest of jobsite conditions, this tool also features a strong magnetic double hook, easy-to-read bold lines, and a retraction brake. |
| Long Description       | Klein Tools Tape Measures deliver performance and durability expected by professional tradespeople. Safeguarded by a thick and durable protective nylon-coating, the Tough Blade has a 16-Foot reach. Able to endure the toughest of jobsite conditions, this tool also features a strong magnetic double hook, easy-to-read bold lines, and a retraction brake. |
| Product Type           | 16' Double Hook Tape Measure   |
| Special Features       | Easy-to-read Bold Lines Every 1/8-Inch; Tough Blade; 16-Foot Reach; Double-sided Blade Printing; Attachment Channel to Tether Tape Measure   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Klein Tools    |
| GTIN                      | 00092644692666 |
| Manufacturers Part Number | 9216           |
| UPC                       | 092644692666   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | HAND TOOLS                               |
| Type                 | Closed Case, Double Sided, Magnetic Hook |

## Packaging

|                 |                 |
|-----------------|-----------------|
| Carton          | 1               |
| Package         | 6               |
| Weight          | 14.7 oz (418 g) |
| Weight Per each | 0.92            |

## Uses, Certifications, and Standards

|             |                    |
|-------------|--------------------|
| Application | Linear Measurement |
|-------------|--------------------|