



Smart Dimmers



Cat. No.	Description
9534	600W Incandescent/Magnetic Low Wattage
9535	600W Electronic Low Voltage
9536	1000W Incandescent/Magnetic Low Wattage
9537	1000W Electronic Low Voltage
9542	Accessory Unit for all ASPIRE Smart Dimmer products

Slide Dimmers & Fan Speed Controls



Cat. No.	Description
9530	600W Incandescent
9531	600W Electronic Low Voltage
9532	1000W Incandescent
9533	1000W Electronic Low Voltage
9538	Lighted 600W Incandescent
9539	Lighted 600W Electronic Low Voltage
9540	Lighted 1000W Incandescent
9541	Lighted 1000W Electronic Low Voltage
9543	5A Fully Variable Fan Speed Control
9544	1.5A Quiet 3-Speed Fan Control

Switches



Cat. No.	Description
9501	Single-Pole, 15A, 120/277V
9503	3-Way Switch, 15A, 120/277V
9504	4-Way Switch, 15A, 120/277V
9511	Lighted Single-Pole, 15A, 120/277V
9513	Lighted 3-Way, 15A, 120/277V
9514	Lighted 4-Way, 15A, 120/277V
9515	Single-Pole, 20A, 120/277V
9516	3-Way Switch, 20A, 120/277V

Mid-Size Screwless Wallplates for ASPIRE™ & ASPIRE RF™

Cat. No.	Description
9521	Single Gang
9522	2-Gang
9523	3-Gang
9524	4-Gang
9525	5-Gang
9526	6-Gang
9527	Blank Insert

Tamper Resistant Receptacles & GFCIs



Cat. No.	Description
9505TR	TR Duplex 15A, 125V
9507TR	TR Single 15A, 125V
9508TR	TR Single 20A, 125V
9510TR	TR Duplex 20A, 125V
9566TR	TR GFCI 15A, 125V
9569TR	TR GFCI 20A, 125V

Communication Outlets



Cat. No.	Description
Inserts	
9545-4	Single Phone Jack Insert
9546-4	Double Phone Jack Insert
9547	Single Coax Adapter Insert
9548-2	Double Coax Adapter Insert
9549-4	Phone/Coax Combo Insert (1 Each) Jack

Jacks & Adapters

(for use with modular wallplates)



9555	Coax F-Connector
9556	Cat 3 Telephone Jack
9557	Cat 5e Data Jack
9558	Blank Insert

Modular Wallplates

9550	1-Port Wallplate
9551	2-Port Wallplate
9552	3-Port Wallplate
9553	4-Port Wallplate
9554	6-Port Wallplate

To indicate color selection, add one of the following suffixes to the Catalog No. when ordering: DS (Desert Sand), SG (Silver Granite), WS (White Satin).

ASPIRE™ Coordinating Screwless Wallplates

Mid-Size
Thermoplastic

FEATURES

- Available in three distinctive colors to coordinate with the rest of the ASPIRE RF product line: White Satin, Desert Sand and Silver Granite. For Alpine White devices, select White Satin wallplates.
- Screwless wallplates clip smoothly into place with gentle pressure.
- Clearly marked top edges make mounting wallplates easy to orient and attach.
- Virtually unbreakable polycarbonate construction.
- Single-gang through six-gang wallplates.
- Standard decorator-sized opening.
- Mid-sized to cover wall imperfections and large wallboard openings.
- Wallplates appear to float freely on the surface of the wall, framing every device beautifully.
- Screw-Catch™ feature holds backplate mounting screws captive for ease of installation.



9521

Mid-Size Screwless ASPIRE Wallplates

Description	Color Suffix	Catalog No.
1-Gang ASPIRE Wallplate	DS, SG, WS	<input type="checkbox"/> 9521__
2-Gang ASPIRE Wallplate	DS, SG, WS	<input type="checkbox"/> 9522__
3-Gang ASPIRE Wallplate	DS, SG, WS	<input type="checkbox"/> 9523__
4-Gang ASPIRE Wallplate	DS, SG, WS	<input type="checkbox"/> 9524__
5-Gang ASPIRE Wallplate	DS, SG, WS	<input type="checkbox"/> 9525__
6-Gang ASPIRE Wallplate	DS, SG, WS	<input type="checkbox"/> 9526__



9522

 cULus Listed to UL5154D, file no. E33216



9527

Blank Wallplate Insert

Description	Color Suffix	Catalog No.
Blank Decorator Insert	DS, SG, WS	<input type="checkbox"/> 9527__

 cULus Listed to UL5154D, file no. E142334

Color Ordering Information: For ordering devices, include Cat. No. followed by the color code: DS (Desert Sand), SG (Silver Granite), WS (White Satin)

Dimensional Information: C-6

Specification Information: Please visit www.cooperwiringdevices.com