


OCCUPANCY & VACANCY SENSORS & TIMERS



Wall Box Timers 125, 125-T, 250 & 277VAC, 60 Hz



97015I

Applications

- Lighting
- Exhaust fans
- Whirlpools and spas
- Saunas
- Heating and heat lamps
- Ventilating and air conditioning

Features

- Units with "Hold" feature may be turned counter-clockwise to hold the load on without timing function.
- Turning clockwise causes unit to time load off after desired time delay.
- Quiet operation.
- Time range from 5 minutes to 1 hour.
- Available with or without hold.
- Decorator styling.
- Easily installed.
- Large head screw terminals.
- Accurate to ± 5 percent.
- Motor rated.
- Energy saving.

CATALOG NUMBER	DESCRIPTION	TIME RANGE	COLOR
DIGITAL TIMERS			
97015I			Ivory
97015W	Timeout, No Hold	15 Minutes	White
97015LA			Light Almond
97030I			Ivory
97030W	Timeout, No Hold	30 Minutes	White
97030LA			Light Almond
97060I			Ivory
97060W	Timeout, No Hold	60 Minutes	White
97115I			Ivory
97115W	Timeout, With Hold	15 Minutes	White
97160I			Ivory
97160W	Timeout, With Hold	60 Minutes	White


CATALOG NUMBER	COLOR
REPLACEMENT KNOBS (WITHOUT PLATE)	
PS55A1	White
PS55B1	Ivory
PS55G1	Light Almond

	VAC	HP
RATINGS		
20 Amp	125	1
10 Amp	250	1
10 Amp	277	
7 Amp	125 Tungsten	

OCCUPANCY & VACANCY SENSORS & TIMERS



Wall Box Timers 125, 125-T, 250 & 277VAC, 60 Hz



97015I

Applications

- Lighting
- Exhaust fans
- Whirlpools and spas
- Saunas
- Heating and heat lamps
- Ventilating and air conditioning

Features

- Units with "Hold" feature may be turned counter-clockwise to hold the load on without timing function.
- Turning clockwise causes unit to time load off after desired time delay.
- Quiet operation.
- Time range from 5 minutes to 1 hour.
- Available with or without hold.
- Decorator styling.
- Easily installed.
- Large head screw terminals.
- Accurate to ± 5 percent.
- Motor rated.
- Energy saving.

CATALOG NUMBER	DESCRIPTION	TIME RANGE	COLOR
DIGITAL TIMERS			
97015I	Timeout, No Hold	15 Minutes	Ivory
97015W			White
97015LA			Light Almond
97030I	Timeout, No Hold	30 Minutes	Ivory
97030W			White
97030LA			Light Almond
97060I	Timeout, No Hold	60 Minutes	Ivory
97060W			White
97115I			Timeout, With Hold
97115W	White		
97160I	Timeout, With Hold	60 Minutes	
97160W			White

CATALOG NUMBER	COLOR
REPLACEMENT KNOBS (WITHOUT PLATE)	
PS55A1	White
PS55B1	Ivory
PS55G1	Light Almond

	VAC	HP
RATINGS		
20 Amp	125	1
10 Amp	250	1
10 Amp	277	
7 Amp	125 Tungsten	