



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A1202HS20PG 12G 1-5/8"X1-5/8" 20FT Pgal BK to BK HS Strut

*Abb Installation Products, Inc*

Catalog Number	A1202HS20PG
Manufacturer	Abb Installation Products, Inc
Description	Channel, 12 Gauge, 1-5/8 Inch X 1-5/8 Inch, Length 20 Feet, Half Slotted Pre-Galvanized Steel With 9/16 Inch X 1-1/8 Inch Slots On 2 Inch Centers, Back to Back Combination
Weight per unit	3.5 (lbs/each)
Product Category	Channel & Strut

### Features

gauge	12 Gauge
-------	----------

### Material, Color, and Finish

Finish	Pre-Galvanized
--------	----------------

### Dimensions and Weight

Depth	1-5/8 In
Length	20 ft
Width	1-5/8 in

### Descriptions

Also Known As...	Strut Strut channel
Description	12G 1-5/8"X1-5/8" 20FT PGAL BK TO BK HS STRUT
extra long description	ABB A1202HS 20PG HALF SLOT CHNL BK-
Long Description	Channel, 12 Gauge, 1-5/8 Inch x 1-5/8 Inch, Length 20 Feet, Half Slotted Pre-Galvanized Steel with 9/16 Inch X 1-1/8 Inch Slots on 2 Inch Centers, Back to Back Combination
Product Type	Half Slot CHNL BK-BK 12GA 20FT PG
similar brands	Unistrut
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces

### Manufacturer Information

Brand	Thomas&Betts-Abb Ins Prod
GTIN	00616013008577
Manufacturers Part Number	A1202HS 20PG
UPC	616013008577

### Taxonomies, Classifications, and Categories

Category Description	STRUT CHANNEL
Type	Metal Channels



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

minimum qty ..... 20 .....

## Packaging

Carton ..... 240 .....

Weight Per foot ..... 3.53 .....

## Uses, Certifications, and Standards

Application ..... Support and framing applications .....