



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A12106PHC 12.1X10.1X6.4 N4X SLD HC

Hoffman Enclosures, Inc.

| | |
|------------------|--|
| Catalog Number | A12106PHC |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Polypro Type 4X, 12.08X10.09X6.38, Polyester |
| Weight per unit | 6.0 (lbs/each) |
| Product Category | Nema Type 1 Metallic Enclosure |

Features

| | |
|-----------|-----------|
| ip rating | IP66 |
| Material | Polyester |

Material, Color, and Finish

| | |
|------------|--------------|
| Color | Light Gray |
| Color Code | RAL 7035 |
| Finish | Smooth Matte |

Dimensions and Weight

| | |
|--------|---------------------|
| Height | 12.08 |
| Size | 12.08x10.08x6.35 in |
| Width | 10.09 |

Descriptions

| | |
|------------------------|--|
| Description | 12.1X10.1X6.4 N4X SLD HC |
| extra long description | NVENT HOF A12106PHC TYPE 4X POLY SO |
| Features | PolyPro polyester enclosures perform exceptionally well in applications where harsh chemicals, weather extremes and corrosive environments demand toughness from a lightweight enclosure. Providing excellent ultraviolet protection and a tight environmental seal, these versatile, feature-rich enclosures are also recyclable. |
| Long Description | PolyPro Type 4X, 12.08x10.09x6.38, Polyester |
| Product Type | Type 4X Poly Solid CVR QR/SC |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510170769 |
| Manufacturers Part Number | A12106PHC |
| UPC | 783510170769 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | PVC BOXES |
| Type | Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 6 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Controls and Drives; Corrosive Environments |
| nema rating | 4X |