



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A200M1CAC A200 - Starter Size 1 Open 3 Pole 120V/60HZ Coil

Eaton Corp

Catalog Number	A200M1CAC
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Motor Control Starter, Non-Reversing Starter, 120V/60 HZ or 110V/50 HZ Coil Voltage, 27A, Three-Pole, Size 1, 2 HP At 115V, 7-1/2 HP At 208, 240V, 10 HP At 480, 600V, A200 Series, Wired For Separate Control
Weight per unit	3.5 (lbs/each)
Product Category	Nema Non-Combination Starters

Features

Poles	Three-pole
-------	------------

Dimensions and Weight

Depth	4.61
Height	3.31
Size	1
Width	4.38

Descriptions

Description	A200 - STARTER SIZE 1 OPEN 3 POLE 120V/60HZ COIL
extra long description	ETN A200M1CAC Non-Reversing Starter
Features	All Class A200 non-reversing starters utilize Type B three-pole overload relays with optional Type A for auto reset applications. Sizes 5 and 6 include the needed current transformers. Moving and stationary contacts are front accessible for simple and easy inspection and maintenance. All Class A200 starters are UL listed and recognized and are CSA certified.
Long Description	Eaton Freedom NEMA motor control starter, Non-reversing starter, 120V/60 Hz or 110V/50 Hz coil voltage, 27A, Three-pole, Size 1, 2 hp at 115V, 7-1/2 hp at 208,240V, 10 hp at 480,600V, A200 series, Wired for Separate Control
Product Type	Non-Reversing Starter
Special Features	Wired for separate control

Manufacturer Information

Brand	Eaton
GTIN	00786678231167
Manufacturers Part Number	A200M1CAC
UPC	786678231167

Taxonomies, Classifications, and Categories

Category Description	FULL VOLTAGE NON-REVERSING Control Starters
----------------------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	3.45

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	CSA Certified,UL Listed