



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A24R248HCR 24X24X8 N3R MD HC

Hoffman Enclosures, Inc.

| | |
|------------------|--|
| Catalog Number | A24R248HCR |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Medium Drip-Shield Hinged-Cover Type 3R, 24.00X24.00X8.00, Gray, Steel |
| Weight per unit | 52.0 (lbs/each) |
| Product Category | Nema Types 3 & 3R Metallic Enc |

Features

| | |
|-----------|------------|
| ip rating | IP32 |
| Material | MILD STEEL |

Material, Color, and Finish

| | |
|------------|------------|
| Color | Gray |
| Color Code | ANSI 61 |
| Finish | Galvanized |

Dimensions and Weight

| | |
|--------|---------------------|
| Depth | 8 |
| Height | 24 |
| Size | 24.00x24.00x8.00 in |
| Width | 24 |

Descriptions

| | |
|------------------------|--|
| Description | 24X24X8 N3R MD HC |
| extra long description | NVENT HOF A24R248HCR Enclosure 24.0 |
| Features | Medium Drip-Shield Hinged-Cover, Type 3R, protects wiring and other electrical components in outdoor applications that require protection from rain, sleet, snow or dripping water. It offers the flexibility of securing enclosure with an optional padlock and collar studs for optional panel mounting. These enclosures have a size range of 16 x 12 x 6-in. to 60 x 36 x 12-in. |
| Long Description | Medium Drip-Shield Hinged-Cover Type 3R, 24.00x24.00x8.00, Gray, Steel |
| Product Type | Enclosure 24.00X24.00X8.00 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510387808 |
| Manufacturers Part Number | A24R248HCR |
| UPC | 783510387808 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------------------|
| Category Description | STEEL JUNCTION BOXES |
| Type | Wall-Mounted / Pad-Mounted Enclosures |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 52 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Controls and Drives; Power Distribution |
| nema rating | 3R Weather-resistant, except dust |