



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A512HW 12HR Spring Wound TMR

Nsi Industries

Catalog Number	A512HW
Manufacturer	Nsi Industries
Description	The Tork A512HW 12-Hour Spring-Wound In-Wall Twist Timer Is Designed to Control A Variety Of Indoor Appliances and Lights. Automate Your Home or Office to Save Energy and Money Using The Simple Twist Knob and Reliable Mechanical Timekeeping. Features A Time Range Of 30 Minutes to 6 Hours and Fits Into A Standard Electrical Box For In-Wall Mounting. Designed For Indoor Loads Such As Lights, Whole House Fans, Air Compressors, Water Heaters or Motors.
Weight per unit	0.0667 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	12 Hour

Dimensions and Weight

Size	H=5.00 - W=3.00
------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	12HR SPRING WOUND TMR
extra long description	TORK A512HW Interval Timer 15 Min I
Features	The TORK A512HW spring-wound in-wall twist timer carries our legacy of innovation and quality with reliable timekeeping and consistent performance. Use twist timers to set a countdown for automatically shutting off appliances or lighting, saving you energy and trouble. No more forgetting to turn off a garage light or attic fan: with a twist timer, simply wind the knob to the correct duration and automate the process. TORK twist timers are at home in residential environments or a range of commercial applica
Long Description	The TORK A512HW 12-Hour Spring-Wound In-Wall Twist Timer is designed to control a variety of indoor appliances and lights. Automate your home or office to save energy and money using the simple twist knob and reliable mechanical timekeeping. Features a time range of 30 minutes to 6 hours and fits into a standard electrical box for in-wall mounting. Designed for indoor loads such as lights, whole house fans, air compressors, water heaters or motors.
Product Type	Interval Timer 15 Min Ivory
Special Features	White 12 Hour No Hold In Wall Time Switch

Manufacturer Information

Brand	NSi
GTIN	00786261151193
Manufacturers Part Number	A512HW
UPC	786261151193

Taxonomies, Classifications, and Categories

Category Description	TIMERS
Type	Spring Wound In Wall Time Switch

Packaging

Carton	1
Weight Per each	0.0667

Uses, Certifications, and Standards

Application	NSI
Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus