



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AGC35R 35A Class R Small Dim Fuse

Bussmann Fuses

Catalog Number	AGC35R
Manufacturer	Bussmann Fuses
Description	Eaton Agc Series Fast-Acting Fuse, 35A, 32 Vac, 32 VDC (Self Certified)
Weight per unit	0.0010 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	35 A
connection	Ferrule End X Ferrule End
dimensions	1.2500 IN X 0.2500 IN X 0.2500 IN
interrupt rating	1 kAIC at 32 Vac
Material	Glass tubeNickel-plated brass end cap construction
Response Time	60 min at 135%, 120 sec at 200%
Voltage Rating	32 Vac, 32 Vdc (self certified)

Descriptions

Description	35A CLASS R SMALL DIM FUSE
extra long description	EFSE AGC-35-R BUSS SMALL DIMENSION
Features	Fast-acting, glass tube 1/4" x 1-1/4" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation. Eaton's AGC fast-acting, glass tube 1/4" x 1-1/4" ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip, or purchase w
Long Description	Eaton AGC series Fast-acting fuse, 35A, 32 Vac, 32 Vdc (self certified)
Product Type	Buss Small Dimension Fuse

Manufacturer Information

Brand	Eaton
GTIN	00051712504287
Manufacturers Part Number	AGC-35-R
UPC	051712504287

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Fast-acting glass tube fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Weight Per each	0.001

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked,RoHS Compliant