



SuperMag™

Magnetic fittings for Superstrut™ metal framing



SilverGalv®



GoldGalv®

To enhance ease of installation, Thomas & Betts introduces their newest innovation— SuperMag magnetic fittings for its Superstrut metal framing line.

Powerful, nickel-plated magnets embedded in the most popular Superstrut steel fittings, including square washers, L-brackets, T-brackets and 90° angle brackets, secure the fitting to the strut during assembly. Acting as a third hand, SuperMag fittings allow the installer to work more efficiently and safely with tools and hardware.


Superstrut SuperMag magnetic fittings—another innovation from Thomas & Betts to help make installation safer, easier and more convenient.

Features and benefits

- Adds convenience and safety to strut assembly by eliminating the need to manually hold fittings and strut together while installing bolts, nuts and rods
- Available in steel with both GoldGalv and SilverGalv finishes
- Features neodymium (NdFeB) grade N35 nickel-plated magnets
- SuperMag fittings support at least 2x their own weight
- Magnets hold in vertical and horizontal orientations
- Magnets are staked in place for dual-sided use

Applications

- New industrial and commercial construction
- Industrial maintenance and repair operations (MRO)
- Commercial building retrofits



AB202M

AB205M

AB219M

AB241M

AB220M

Superstrut SuperMag magnetic fittings — steel with GoldGalv or SilverGalv finish

Catalog no.	Description	Std. pkg. qty.	UPC no.
AB202M	Magnetic 90° angle fitting, 2-hole, 1 $\frac{1}{8}$ "H x 2"L, GoldGalv®	50	616013-13357
AB202M EG	Magnetic 90° angle fitting, 2-hole, 1 $\frac{1}{8}$ "H x 2"L, SilverGalv®	50	616013-13358
AB205M	Magnetic 90° angle fitting, 4-hole, 4 $\frac{1}{8}$ "H x 3- $\frac{1}{2}$ "L, GoldGalv®	25	616013-13359
AB205M EG	Magnetic 90° angle fitting, 4-hole, 4 $\frac{1}{8}$ "H x 3- $\frac{1}{2}$ "L, SilverGalv®	25	616013-13360
AB219M	Magnetic flat L-bracket, GoldGalv®	25	616013-13361
AB219M EG	Magnetic flat L-bracket, SilverGalv®	25	616013-13362
AB220M	Magnetic flat T-bracket, GoldGalv®	25	616013-13363
AB220M EG	Magnetic flat T-bracket, SilverGalv®	25	616013-13364
AB241M 1/4	Magnetic square washer for 1/4" bolt, GoldGalv®	100	616013-13369
AB241M 1/4 EG	Magnetic square washer for 1/4" bolt, SilverGalv®	100	616013-13370
AB241M 3/8	Magnetic square washer for 3/8" bolt, GoldGalv®	100	616013-13367
AB241M 3/8 EG	Magnetic square washer for 3/8" bolt, SilverGalv®	100	616013-13368
AB241M 1/2	Magnetic square washer for 1/2" bolt, GoldGalv®	100	616013-13365
AB241M 1/2 EG	Magnetic square washer for 1/2" bolt, SilverGalv®	100	616013-13366

Note: The magnets are only intended for use as an installer aid, not as a permanent installation method on their own. Magnetic fittings must be bolted in place following the same standard installation procedures as non-magnetic fittings for permanent installation.

Standard finish is GoldGalv. For SilverGalv, please specify suffix EG when ordering. Best for use with traditional or spring channel nuts.

Please ask your Thomas & Betts sales representative for a complete catalog of quality Thomas & Betts electrical products or visit us at www.tnb.com. For customer service, call 1-800-816-7809. For technical questions, call 1-888-862-3289.

© 2017 Thomas & Betts Corporation. All rights reserved. Printed in the U.S.A.
5/17 GM7726

Thomas & Betts Corporation
Electrification Products Division of ABB
8155 T&B Boulevard
Memphis, TN 38125
901-252-5000
www.tnb.com

Thomas & Betts
A Member of the ABB Group