



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AH1222V SW Toggle DP 20A 120/277V Autogrd B&S Iv *Eaton Wiring Devices*

Catalog Number	AH1222V
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Industrial Grade Toggle Switch, #14-10 Awg, 20A, Industrial, Flush, 120/277V, Back and Side, Screw, Ivory, Double-Pole, Dual-Pole, Brass, Polycarbonate
Weight per unit	0.0010 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	20
dimensions	1.3000 IN X 1.0050 IN X 4.1900 IN
Material	Polycarbonate
media	Yes
Poles	2
Voltage Rating	120/277 V

### Material, Color, and Finish

Color	Ivory
-------	-------

### Descriptions

Description	SW TOGGLE DP 20A 120/277V AUTOGRD B&S IV
extra long description	EWD AH1222V SW Toggle DP 20A 120/27
Features	Eaton's Arrow Hart broad line of extra heavy-duty industrial grade switches feature superior engineering, reliable performance and ease of installation. Available in toggle, lighted, pilot light, Corbin and locking versions.
Long Description	Eaton Arrow Hart industrial grade toggle switch, #14-10 AWG, 20A, Industrial, Flush, 120/277V, Back and side, Screw, Ivory, Double-Pole, Dual-pole, Brass, Polycarbonate
Product Type	SW Toggle DP 20A 120/277V Autogrd B&S Iv
Special Features	Commercial Grade

### Manufacturer Information

Brand	Eaton Wiring Devices
GTIN	00032664734755
Manufacturers Part Number	AH1222V
UPC	032664734755

### Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Industrial grade toggle switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.001

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
standard	cULus Listed,NAFTA