



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 North East 20th Ave.
76067-0000, TX Mineral Wells
Phone: 940-325-5503
Fax: 940-325-5544



AN13KN0A5E100 Space SVG Nema Size 3 STR 120V Coil 20-100a *Eaton Corp*

Catalog Number	AN13KN0A5E100
Manufacturer	Eaton Corp
Description	Eaton Space-Saving Nema Starter, Full Voltage Non-Reversing, Xtoe Electronic Overload Relay, Nema Size 3 Open Enclosure - 90 A, Horizontal Mounting, 120/60 or 110/50 Coil Voltage, C440 Standard Feature Set - 20-100 A
Weight per unit	1.0 (lbs/each)
Product Category	Nema Combination Starters

Features

Coil Voltage	120/60 or 110/50
--------------	------------------

Dimensions and Weight

Depth	5.5
Height	6.3
Size	NEMA size 1C
Width	1.77

Descriptions

Description	SPACE SVG NEMA SIZE 3 STR 120V COIL 20-100A
extra long description	ETN AN13KN0A5E100 NEMA SZ3, STR, 12
Features	Eaton's Freedom starters and contactors feature a compact, space-saving design, using state-of-the-art technology and the latest in high strength, impact and temperature resistant insulating materials. In addition to the bimetallic overload, Eaton also offers a series of electronic overload relay (C440) available as a standalone unit and assembled with Freedom contactor. These adjustable bimetallic ambient compensated contactors are designed for use with CE or CN non-reversing and reversing contactors. The
Long Description	Eaton Space-Saving NEMA Starter, Full voltage non-reversing, XTOE electronic overload relay, NEMA Size 3 open enclosure - 90 A, Horizontal mounting, 120/60 or 110/50 coil voltage, C440 standard feature set - 20-100 A
Product Type	Nema SZ3, STR, 120V Coil, 20-100a

Manufacturer Information

Brand	Eaton
GTIN	00786685629551
Manufacturers Part Number	AN13KN0A5E100
UPC	786685629551



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 North East 20th Ave.
76067-0000, TX Mineral Wells
Phone: 940-325-5503
Fax: 940-325-5544

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
NEMA Frame Size	NEMA Size 3
standard	CSA Certified,UL Listed