




SPECIFICATIONS
ASHSG
 EXHAUST FAN HOUSING

Exhaust Fan Housing

- **Fan Housing**
 23 gauge galvanized metal housing.
 Dimensions 7 1/4" x 7 1/4" x 3 3/4".
- **Duct Collar**
 Plastic collar for 3" duct connection, comes complete with built in non-metallic back draft damper for quiet operation.
- **Unit Mounting**
 Rated for ceilings insulated to R-40. Designed to mount in ceilings or walls with at least 4" of clearance. The housing will mount through drywall thickness up to 3/4", with a rough-in opening of 7 1/2" x 7 1/2".
- **Electrical Connections**
 1/2" electrical knockouts provided.
- **Available Trim Kits**
 AS50MBG: 50 CFM
 AS60MBG: 60 CFM
 AS70MBG: 70 CFM
- **Shipping Info**
 Number of Housings in Box: 6
 UPC Code: 083162222619



Housing ONLY. Must be combined with ASMBG series trim kit (sold separately)

| PROJECT | | | | | ARCHITECT | | | | |
|-------------------|--------------|-----|---------|-----|---------------------|------|-------|-------------|------------------------------|
| | | | | | | | | | |
| LOCATION | | | | | ENGINEER | | | | |
| | | | | | | | | | |
| CONTRACTOR | | | | | SUBMITTED BY | | | DATE | |
| | | | | | | | | | |
| FAN NUMBER | MODEL NUMBER | CFM | IN W.G. | RPM | WATTS | AMPS | SONES | QTY | OPTIONAL EQUIPMENT & REMARKS |
| | | | | | | | | | |




820 Lincoln Avenue
 West Chester, Pennsylvania 19380-4466
 Tel: (610) 692-7400 • 877-304-3785
 Fax: (610) 696-8048



SPECIFICATIONS
ASHSG
 EXHAUST FAN HOUSING

Exhaust Fan Housing

- **Fan Housing**
 23 gauge galvanized metal housing.
 Dimensions 7 1/4" x 7 1/4" x 3 3/4".
- **Duct Collar**
 Plastic collar for 3" duct connection, comes complete with built in non-metallic back draft damper for quiet operation.
- **Unit Mounting**
 Rated for ceilings insulated to R-40. Designed to mount in ceilings or walls with at least 4" of clearance. The housing will mount through drywall thickness up to 3/4", with a rough-in opening of 7 1/2" x 7 1/2".
- **Electrical Connections**
 1/2" electrical knockouts provided.
- **Available Trim Kits**
 AS50MBG: 50 CFM
 AS60MBG: 60 CFM
 AS70MBG: 70 CFM
- **Shipping Info**
 Number of Housings in Box: 6
 UPC Code: 083162222619



Housing ONLY. Must be combined with ASMBG series trim kit (sold separately)

| PROJECT | | | | | ARCHITECT | | | | |
|-------------------|--------------|-----|---------|-----|---------------------|------|-------|-------------|------------------------------|
| | | | | | | | | | |
| LOCATION | | | | | ENGINEER | | | | |
| | | | | | | | | | |
| CONTRACTOR | | | | | SUBMITTED BY | | | DATE | |
| | | | | | | | | | |
| FAN NUMBER | MODEL NUMBER | CFM | IN W.G. | RPM | WATTS | AMPS | SONES | QTY | OPTIONAL EQUIPMENT & REMARKS |
| | | | | | | | | | |



820 Lincoln Avenue
 West Chester, Pennsylvania 19380-4466
 Tel: (610) 692-7400 • 877-304-3785
 Fax: (610) 696-8048