



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ATD2000CL Occsens, DT, CLNG, LN, Voltage, 2000' *Hubbell Wiring Devices*

Catalog Number	ATD2000CL
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Control, H-Moss, Occupancy Sensor, Adaptive Dual Tech, Ceiling Mount, 2000 Square Feet, 120V Ac
Weight per unit	0.6320 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

connector	Screwed Terminal
load	Lighting Circuit
pallet quantity	624
supply voltage	120/277 AC
Voltage Rating	120-277

Material, Color, and Finish

Color	White
-------	-------

Descriptions

Description	OCCSENS,DT,CLNG,LN,VOLTAGE,2000'
extra long description	HWDK ATD2000CL OCCSENS,DT,CLNG,LN,V
Features	Adaptive Dual Technology combines Ultrasonic and Passive Infrared technology, minimizing the risk of lights turning ON when the space is unoccupied. Once occupancy is detected by both technologies within the space lights are turned ON, only one technology is necessary to keep the lights ON. Adaptive technology provides better control. Hubbell's patented breakthrough in advanced control feature smart microprocessors constantly monitoring the controlled area and adjust the sensitivity and timer based on envi
Long Description	Switches and Lighting Control, H-MOSS,Occupancy Sensor, Adaptive Dual Tech, Ceiling Mount, 2000 Square Feet,120V AC
Product Type	Occsens, DT, CLNG, LN, Voltage, 2000 SQ FT
Special Features	Occupancy

Manufacturer Information

Brand	Hubbell Wiring Device-Kellems
GTIN	00783585256900
Manufacturers Part Number	ATD2000CL
series	Dual
UPC	783585256900



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Sensors

Packaging

Carton	1
Package	12
Weight Per each	0.632

Uses, Certifications, and Standards

Application	Single Circuit
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Mounting Screws
standard	UL/CSA