



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



B2008PASS4 BLTF 1/2" Pa SS4 Rigid Pipe Clamp

Cooper B-Line/Cable Tray

Catalog Number	B2008PASS4
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Pre-Assembled O.D. Pipe and Conduit Clamp, 0.0590" H X 2.3960" L X 1.25" W, Steel, Stainless Steel Type 304
Weight per unit	0.0010 (lbs/each)
Product Category	Channel & Strut Fittings

Features

dimensions	2.3960 IN X 1.2500 IN X 0.0590 IN
Material	304 Stainless Steel

Material, Color, and Finish

Finish	STAINLESS STEEL TYPE 304
--------	--------------------------

Dimensions and Weight

Size	1/2 in
------	--------

Descriptions

Construction	TWO PIECE
Description	BLTF 1/2" PA SS4 RIGID PIPE CLAMP
extra long description	B-LINE B2008PASS4 1/2" PIPE/CONDUIT
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series pre-assembled O.D. pipe and conduit clamp, 0.0590" H x 2.3960" L x 1.25" W, Steel, Stainless steel type 304
Product Type	1/2" Pipe/Conduit Clamp, Rigid, 1/2", Pre-Asm, SSL
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut

Manufacturer Information

Brand	Eaton
GTIN	00781011871864
Manufacturers Part Number	B2008PASS4
UPC	781011871864

Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Pre-assembled O.D. pipe and conduit clamp

Packaging

Carton	1
Weight Per each	0.001



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting standard	CHANNEL Not Applicable