



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



B2011SS4114RGD BLTD 1-1/4" SS4 Rigid Pipe Clamp

Cooper B-Line/Cable Tray

Catalog Number	B2011SS4114RGD
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series O.D. Pipe and Conduit Clamp, 0.0740" H X 3.3510" L X 1.25" W, Steel, 600 LBS Load Cap
Weight per unit	0.2000 (lbs/each)
Product Category	Channel & Strut Fittings

Features

dimensions	3.3510 IN X 1.2500 IN X 0.0740 IN
Material	304 Stainless Steel

Material, Color, and Finish

Finish	STAINLESS STEEL TYPE 304
--------	--------------------------

Dimensions and Weight

Size	1-1/4 in
------	----------

Descriptions

Construction	TWO PIECE
Description	BLTD 1-1/4" SS4 RIGID PIPE CLAMP
extra long description	B-LINE B2011SS4 1 1/4"-RIGID CONDUIT
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series O.D. pipe and conduit clamp, 0.0740" H x 3.3510" L x 1.25" W, Steel, 600 Lbs load cap
Product Type	1 1/4"-Rigid Conduit Clamp, 1 1/4", SSL 304
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut

Manufacturer Information

Brand	Eaton
GTIN	00781011601331
Manufacturers Part Number	B2011SS4
UPC	781011601331

Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	O.D. pipe and conduit clamp

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting standard	CHANNEL Not Applicable