



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AYCL253PWH Ariadni 250W Led 3WAY White

Lutron

Catalog Number	AYCL253PWH
Manufacturer	Lutron
Description	Ariadni Dimmer For 250W CFL/Led, 600W Inc/Hal, or Lutron Hi-Lume A-Series Lte Led Driver In White
Weight per unit	0.3500 (lbs/each)
Product Category	Lighting Dimmers

Features

Connection Type	Screw Terminal
insulation	Plastic
media	Yes
Poles	1
Switch Type	Toggle
Voltage Rating	120
Wattage	600

Dimensions and Weight

Size	4.60 x 2.86;117 x 73
------	----------------------

Descriptions

Description	ARIADNI 250W LED 3WAY WHITE
extra long description	LUT AYCL-253P-WH ARIADNI CFL/LED 25
Features	The Ariadni LED+ dimmer switch works with dimmable LED and CFL screw-in bulbs up to 250-Watt and is also compatible with up to 600-Watt of standard incandescent and halogen bulbs, allowing you to control all 4 bulb types on the same circuit. It is designed to control a broad range of dimmable LED and CFL bulbs from a variety of brands including Philips, Cree, GE, Eco Smart and Lighting Science. The Ariadni/Toggler LED+ dimmer switch matches your existing toggle switches. It features a slider to adjust your
Long Description	Ariadni dimmer for 250W CFL/LED, 600W inc/hal, or Lutron Hi-Lume A-Series LTE LED Driver in white
Product Type	Ariadni CFL/Led 250W White
Special Features	Controls 250 W LED/CFL (screw-base), 600 W incandescent/halogen or 350 W Hi-Lume 1 percent 2-wire LED driver loads. Toggle turn lights on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs as well as halogens and incandescents.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lutron
GTIN	00784276090100
Manufacturers Part Number	AYCL253PWH
UPC	784276090100

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Preset dimmer, 3-way/single-pole

Packaging

Carton	1
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Mounting	WALLBOX
standard	UL1472 CSA C22.2 184.1, NEMA SSL-7A Type 2