



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



B2212PAZN BLTD 1-1/2" Zinc Plate Pre-Assemb Unv Pipe Clamp

Cooper B-Line/Cable Tray

Catalog Number	B2212PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Multi-Grip/Offset Pipe Clamp, 0.0966" H X 3.3750" L X 1.25" W, Steel, 600 LBS Load, Pipe Clamp For Thinwall (Emt)
Weight per unit	0.2300 (lbs/each)
Product Category	Channel & Strut Fittings

Features

dimensions	3.3750 IN X 1.2500 IN X 0.0966 IN
Material	12 Gauge Low Carbon Steel

Material, Color, and Finish

Finish	Pre-Galvanized
--------	----------------

Dimensions and Weight

Size	1-1/2 in
------	----------

Descriptions

Construction	TWO PIECE
Description	BLTD 1-1/2" ZINC PLATE PRE-ASSEMB UNV PIPE CLAMP
extra long description	B-LINE B2212PAZN 1 1/2" MULTI-GRIP
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series multi-grip/offset pipe clamp, 0.0966" H x 3.3750" L x 1.25" W, Steel, 600 Lbs load, Pipe clamp for thinwall (EMT)
Product Type	1 1/2" Multi-Grip Pipe Clamp, Pre-Asm, Thinwall
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut, Pipe Range 1.735 To 1.931 In OD, Load Capacity 600 Lb Vertical, 75 Lb Transverse

Manufacturer Information

Brand	Eaton
GTIN	00781011605445
Manufacturers Part Number	B2212PAZN
UPC	781011605445

Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Multi-grip and offset pipe clamp



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.23

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable