



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## B2019PAZN BLTD 5" Zinc Plate Pa Rigid Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2019PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Pre-Assembled O.D. Pipe and Conduit Clamp, 0.12" H X 7.9690" L X 1.25" W, Stainless Steel, 1000 LBS Load Cap
Weight per unit	0.0192 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	7.9690 IN X 1.2500 IN X 0.1200 IN
Material	11 Gauge Low Carbon Steel

### Material, Color, and Finish

Finish	Pre-Galvanized
--------	----------------

### Dimensions and Weight

Size	5 in
------	------

### Descriptions

Construction	TWO PIECE
Description	BLTD 5" ZINC PLATE PA RIGID PIPE CLAMP
extra long description	B-LINE B2019PAZN 5" PIPE/CONDUIT CL
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series pre-assembled O.D. pipe and conduit clamp, 0.12" H x 7.9690" L x 1.25" W, Stainless steel, 1000 Lbs load cap
Product Type	5" Pipe/Conduit Clamp, Pre-Asm, Rigid, 5", ZN PLTD
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut

### Manufacturer Information

Brand	Eaton
GTIN	00781011611248
Manufacturers Part Number	B2019PAZN
UPC	781011611248

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Pre-assembled O.D. pipe and conduit clamp

### Packaging

Carton	1
Weight Per each	0.0192



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting standard	CHANNEL Not Applicable