



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **B2209ZN BLTD 3/4"-Multi-Grip Pipe CLMP Thinwall, Inc, Rig**

*Cooper B-Line/Cable Tray*

Catalog Number	B2209ZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Multi-Grip/Offset Pipe Clamp, 0.0677" H X 2.3750" L X 1.25" W, Steel, 400 LBS Load Cap, Pipe Clamp For Thinwall (Emt)
Weight per unit	0.1200 (lbs/each)
Product Category	Channel & Strut Fittings

### **Features**

dimensions	2.3750 IN X 1.2500 IN X 0.0677 IN
Material	14 Gauge Low Carbon Steel

### **Material, Color, and Finish**

Finish	Pre-Galvanized
--------	----------------

### **Dimensions and Weight**

Size	3/4 in
------	--------

### **Descriptions**

Construction	TWO PIECE
Description	BLTD 3/4"-MULTI-GRIP PIPE CLMP THINWALL, IMC, RIG
extra long description	B-LINE B2209ZN 3/4"-MULTI-GRIP PIPE
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series multi-grip/offset pipe clamp, 0.0677" H x 2.3750" L x 1.25" W, Steel, 400 Lbs load cap, Pipe clamp for thinwall (EMT)
Product Type	3/4"-Multi-Grip Pipe Clamp, Thinwall, Inc, Rigid, ZN PLTD
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut, Pipe Range 0.917 To 1.081 In OD, Load Capacity 400 Lb Vertical, 50 Lb Transverse

### **Manufacturer Information**

Brand	Eaton
GTIN	00781011604233
Manufacturers Part Number	B2209ZN
UPC	781011604233

### **Taxonomies, Classifications, and Categories**

Category Description	MISC FITTINGS
Type	Multi-grip and offset pipe clamp



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.12

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable