



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB1020S Bab BRKR 1P 20A Max 240V Max 10K Aic *Eaton Corp*

Catalog Number	BAB1020S
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 20 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab, 24/48 VDC Shunt Trip
Weight per unit	1.0 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

Features

dimensions	3.9000 IN X 2.2000 IN X 4.8000 IN
interrupt rating	10
media	Yes
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	BAB BRKR 1P 20A MAX 240V MAX 10K AIC
extra long description	ETN BAB1020S BAB BREAKER 1P 20A MAX
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,20 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB,24/48 Vdc Shunt trip
Product Type	Bab Breaker 1P 20A Max 240V Max 10K Aic
Special Features	Bolt-on mounting

Manufacturer Information

Brand	Eaton
GTIN	00786679509609
Manufacturers Part Number	BAB1020S
UPC	786679509609

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional
EnergyOtherMarine Vessels and Equipment - Marine Vessels and
Equipment - OtherGeneration - Renewable Energy - Alternative
EnergyDatacenters - IT Space: CI and Hyper ConvergedResidential
Bldgs & Facilities - Residential Bldgs & Facilities - Other

standard

UL Listed,CSA Certified