



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street  
79735-0000, TX Fort Stockton  
Phone: 432-336-8730  
Fax: 432-336-3279



## **BAB2070 BRKR 2 Pole 70a** *Eaton Corp*

Catalog Number	BAB2070
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, 70 A, 3 Kaic, Two-Pole, 240/415 V, Non-Interchangeable, Q7, Bab
Weight per unit	1.5 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

### **Features**

dimensions	3.6000 IN X 2.2000 IN X 3.7000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

### **Descriptions**

Description	BRKR 2 POLE 70A
extra long description	ETN BAB2070 BRKR 2 Pole 70 Amp
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting,70 A,3 kAIC,Two-pole,240/415 V,Non-Interchangeable,Q7,BAB
Product Type	BRKR 2 Pole 70 Amp
Special Features	Bolt-on mounting

### **Manufacturer Information**

Brand	Eaton
GTIN	00786679302705
Manufacturers Part Number	BAB2070
UPC	786679302705

### **Taxonomies, Classifications, and Categories**

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

### **Availability**

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street  
79735-0000, TX Fort Stockton  
Phone: 432-336-8730  
Fax: 432-336-3279

## Packaging

Carton	1
Package	24
Weight Per each	1.5

## Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional Energy Generation - Renewable Energy - Alternative Energy Other Marine Vessels and Equipment - Marine Vessels and Equipment - Other Datacenters - IT Space: CI and Hyper Converged Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	CSA Certified, UL Listed