



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1501 North Cypress Street
72114-0000, AR N. Little Rock
Phone: 501-945-9398
Fax: 501-508-2426



BAB3020H BAB3020H BRKR A

Eaton Corp

Catalog Number	BAB3020H
Manufacturer	Eaton Corp
Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, 20A, Bab Type, 10 Kaic, Bolt-On Mounting, Three-Pole, Non-Interchangeable, 240V
Weight per unit	1.0 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

Features

dimensions	3.3750 IN X 3.0000 IN X 3.5000 IN
interrupt rating	10
media	Yes
Poles	Three-pole
Voltage Rating	240 V - 240 V

Descriptions

Description	BAB3020H BRKR A
extra long description	ETN BAB3020H BAB3020H BRKR A
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, 20A, BAB type, 10 kAIC, Bolt-on mounting, Three-pole, Non-Interchangeable, 240V
Product Type	BAB3020H BRKR A
Special Features	Bolt-on mounting

Manufacturer Information

Brand	Eaton
GTIN	00786679303207
Manufacturers Part Number	BAB3020H
UPC	786679303207

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1501 North Cypress Street
72114-0000, AR N. Little Rock
Phone: 501-945-9398
Fax: 501-508-2426

Packaging

Carton	1
Weight Per each	1.03

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional Energy Datacenters - IT Space: CI and Hyper Converged Generation - Renewable Energy - Alternative Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other Other Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	CSA Certified, UL Listed