



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB3025H BAB3025H BRKR A**

*Eaton Corp*

|                  |  |
|------------------|--|
| Catalog Number   | BAB3025H   |
| Manufacturer     | Eaton Corp   |
| Description      | Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial, 25A, 10 Kaic, Bolt-On Mounting, Three-Pole, Non-Interchangeable, 240V |
| Weight per unit  | 1.0 (lbs/each)   |
| Product Category | 3 Pole Standard Trip Bolt-On   |

### **Features**

|                  |                                   |
|------------------|-----------------------------------|
| amperage rating  | 25 A                              |
| dimensions       | 3.5000 IN X 3.2000 IN X 3.0000 IN |
| interrupt rating | 10                                |
| media            | Yes                               |
| Poles            | 3                                 |
| Trip Type        | Non-Interchangeable               |
| Voltage Rating   | 240 V - 240 V                     |

### **Descriptions**

|                        |  |
|------------------------|--|
| Description            | BAB3025H BRKR A  |
| extra long description | ETN BAB3025H Thermal-Magnetic Circu  |
| Features               | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description       | Eaton BAB thermal magnetic circuit breaker, Quicklag Industrial, 25A, 10 kAIC, Bolt-on mounting, Three-pole, Non-Interchangeable, 240V   |
| Product Type           | Thermal-Magnetic Circuit Breaker, 25a  |
| Special Features       | Bolt-on mounting   |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786679303252 |
| Manufacturers Part Number | BAB3025H       |
| UPC                       | 786679303252   |

### **Taxonomies, Classifications, and Categories**

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS        |
| Type                 | Thermal magnetic circuit breakers |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 1 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | OtherGeneration - Renewable Energy - Alternative<br>EnergyGeneration - Conventional Energy - Conventional<br>EnergyMarine Vessels and Equipment - Marine Vessels and<br>Equipment - OtherDatacenters - IT Space: CI and Hyper<br>ConvergedResidential Bldgs & Facilities - Residential Bldgs &<br>Facilities - Other |
| standard    | UL Listed,CSA Certified  |