



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB3070H Bab 3-Pole 70A MCB**

*Eaton Corp*

Catalog Number	BAB3070H
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 70 A, 10 Kaic, Three-Pole, 240 V, Interchangeable, Bab, Distribution Panels 240V (Three-Phase, Four-Wire Maximum), Four-Wire, Three-Phase
Weight per unit	1.1 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

### **Features**

dimensions	3.9000 IN X 3.2000 IN X 4.9000 IN
interrupt rating	10
media	Yes
Poles	3
Voltage Rating	240 V - 240 V

### **Descriptions**

Description	BAB 3-POLE 70A MCB
extra long description	ETN BAB3070H 70A, 3 pole circuit br
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,70 A,10 kAIC,Three-pole,240 V,Interchangeable,BAB,Distribution panels 240V (Three-phase, four-wire maximum),Four-wire,Three-phase
Product Type	70A, 3 Pole Circuit Breaker, Pow-R-Line
Special Features	Bolt-on mounting

### **Manufacturer Information**

Brand	Eaton Corp
GTIN	00786679303702
Manufacturers Part Number	BAB3070H
UPC	786679303702

### **Taxonomies, Classifications, and Categories**

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	8
Weight Per each	1.05

## Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	CSA Certified,UL Listed