



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BAB2060 BAB2060 BRKR A

Eaton Corp

|                  |  |
|------------------|--|
| Catalog Number   | BAB2060  |
| Manufacturer     | Eaton Corp   |
| Description      | Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, High Intensity Discharge, 60 A, 10 Kaic, Two-Pole, 120/240 V, Non-Interchangeable, Q7, Bab |
| Weight per unit  | 1.4 (lbs/each)   |
| Product Category | 2 Pole Standard Trip Bolt-On   |

### Features

|                  |                                   |
|------------------|-----------------------------------|
| dimensions       | 3.8000 IN X 2.2000 IN X 4.8000 IN |
| interrupt rating | 10                                |
| Poles            | 2                                 |
| Voltage Rating   | 120/240 V                         |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | BAB2060 BRKR A   |
| extra long description | ETN BAB2060 60A, 2 pole circuit bre  |
| Features               | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description       | Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting, High intensity discharge,60 A,10 kAIC,Two-pole,120/240 V,Non-Interchangeable,Q7,BAB  |
| Product Type           | 60A, 2 Pole Circuit Breaker, Pow-R-Line  |
| Special Features       | Bolt-on mounting   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786679302606 |
| Manufacturers Part Number | BAB2060        |
| UPC                       | 786679302606   |

### Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS        |
| Type                 | Thermal magnetic circuit breakers |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 1.4 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative Energy  
Generation - Conventional Energy - Conventional Energy  
Other Datacenters - IT Space: CI and Hyper Converged  
Marine Vessels and Equipment - Marine Vessels and Equipment - Other  
Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other

standard

CSA Certified, UL Listed