



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB3015H 3P 15A Bab BRKR

Eaton Corp

Catalog Number	BAB3015H
Manufacturer	Eaton Corp
Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, 15A, Bab Type, 10 Kaic, Bolt-On Mounting, Three-Pole, Non-Interchangeable, 240V
Weight per unit	1.0 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

Features

dimensions	3.8000 IN X 3.2000 IN X 4.9000 IN
interrupt rating	10
media	Yes
Poles	3
Voltage Rating	240 V - 240 V

Descriptions

Description	3P 15A BAB BRKR
extra long description	ETN BAB3015H 15A, 3 pole circuit br
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, 15A, BAB type, 10 kAIC, Bolt-on mounting, Three-pole, Non-Interchangeable, 240V
Product Type	15A, 3 Pole Circuit Breaker, Pow-R-Line
Special Features	Bolt-on mounting

Manufacturer Information

Brand	Eaton Corp
GTIN	00786679303153
Manufacturers Part Number	BAB3015H
UPC	786679303153

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	8
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Marine Vessels and Equipment - Marine Vessels and Equipment -
OtherGeneration - Renewable Energy - Alternative
EnergyOtherDatacenters - IT Space: CI and Hyper
ConvergedGeneration - Conventional Energy - Conventional
EnergyResidential Bldgs & Facilities - Residential Bldgs & Facilities
- Other

standard

UL Listed,CSA Certified