



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BABF1020 Fire Alarm BRKR Per Nfpa 72

Eaton Corp

Catalog Number	BABF1020
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Classic Replacement Circuit Breaker, 15 A, 10 Kaic At 120/240 V, Single-Pole, 120/240 V, #14-8 Awg Cu/Al, BQL
Weight per unit	0.3500 (lbs/each)
Product Category	On Circuit Breakers

Features

dimensions	3.2500 IN X 0.8750 IN X 3.5000 IN
interrupt rating	10 kAIC
media	Yes
Poles	Single-pole
Voltage Rating	120/240 V

Descriptions

Description	FIRE ALARM BRKR PER NFPA 72
extra long description	ETN BABF1020 FIRE ALARM BREAKER PER
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker, Classic replacement circuit breaker, 15 A, 10 kAIC at 120/240 V, Single-pole, 120/240 V, #14-8 AWG Cu/Al, BQL
Product Type	Fire Alarm Breaker Per Nfpa 72

Manufacturer Information

Brand	Eaton
GTIN	00786685405063
Manufacturers Part Number	BABF1020
UPC	786685405063

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Marine Vessels and Equipment - Marine Vessels and Equipment -
OtherOtherGeneration - Renewable Energy - Alternative
EnergyGeneration - Conventional Energy - Conventional
EnergyDatacenters - IT Space: CI and Hyper ConvergedResidential
Bldgs & Facilities - Residential Bldgs & Facilities - Other

standard

UL Listed,NFPA 72,HACR Rated