



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BG88 2-1/2" to 3" Body CVR&GSKT *Crouse-Hinds*

Catalog Number	BG88
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet B Mogul Blank Cover, Feraloy Iron Alloy, Round Neoprene Gasket, 2-1/2" or 3"
Weight per unit	7.5 (lbs/each)
Product Category	Bodies & Covers

Features

Material	FERALOY IRON ALLOY
----------	--------------------

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Dimensions and Weight

Height	17
Length	4.25
Width	1.46

Descriptions

Description	2-1/2" TO 3" BODY CVR&GSKT
extra long description	CRS-H BG88 2 1/2 OR 3 IRON MOGUL CV
Features	Crouse-Hinds series mogul bodies are installed in conduit systems to act as pull outlets for conductors that are stiff due to large size or type of insulation. Mogul bodies provide longer openings needed when pulling large conductors and prevent sharp bends and kinks during installation. Mogul conduit bodies are manufactured in trade sizes 1/2" to 6" and are available in Feraloy iron alloy and copper-free aluminum. Our iron alloy bodies are available with a hot dip galvanized finish for added corrosion
Long Description	Eaton Crouse-Hinds series Condulet B mogul blank cover, Feraloy iron alloy, Round neoprene gasket, 2-1/2" or 3"
Product Type	2 1/2 or 3 Iron Mogul CVR/Gask
Special Features	Round neoprene gasket

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274102108
Manufacturers Part Number	BG88
UPC	782274102108

Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Mogul blank cover



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	4
Weight Per each	7.45

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D